


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Part No.	Description	
1	SPSM-41T-M1.1	PSI Connector - Male Contact	
2	SPSI-41T-M1.1	PSI Connector - Female Contact	
3	UL1007, 16 AWG	Black	

Electrical Specifications
Current: 12.0AAC/DC
Voltage: 300V AC/DC

APPLICABLE HOUSINGS				
NO. OF CIRCUITS	KEYING	FEMALE CONTACT HOUSING PART NO.	MALE CONTACT HOUSING PART NO.	HOUSING COLOR
2	A	PSIP-02V-LE-A	PSIR-02V-LE-A	LIGHT BLUE
	B	PSIP-02V-Y-B	PSIR-02V-Y-B	YELLOW
3	A	PSIP-03V-LE-A	PSIR-03V-LE-A	LIGHT BLUE
	B	PSIP-03V-Y-B	PSIR-03V-Y-B	YELLOW



ZONE	REV	DESCRIPTION	DATE	APPROVED
1	1	Add Electrical Specifications	7/02/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.	CUSTOMER NAME			
	DESCRIPTION			
Drawn By: Larissa Mosley		SIZE	CUSTOMER PART NO.	PART NO.
Checked By: Steven Pilkington		SCALE	1:1	DATE
		DRAWING NO. GAM-417		5/23/2018

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[ASPSISPSM16K254](#)