

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

Item No.	Part No.	Description
1	SVF-61T-P2.0	VL Connector Female Contact
2	UL1015, 14 AWG	Black


Electrical Specifications

Current: 20.0A AC/DC

Voltage: 600V AC/DC

APPLICABLE HOUSINGS

NO. OF CIRCUITS	HOUSING PART NO. INNER LOCKS	HOUSING PART NO. OUTER LOCKS
1	VLP-01V	VLP-01V-1
2	VLP-02V	VLP-02V-1
3	VLP-03V	VLP-03V-1
4	VLP-04V	VLP-04V-1
4	-	VLP-04VN-1
6	VLP-06V	VLP-06V-1
8	VLP-08V	VLP-08V-1
12	VLP-12V	VLP-12V-1



JST

ZONE	REV	DESCRIPTION	DATE	APPROVED
1	1	Add Electrical Specifications	7/03/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.		CUSTOMER NAME		
		DESCRIPTION		
Drawn By: Larissa Mosley		SIZE	CUSTOMER PART NO.	PART NO.
Checked By: Steven Pilkington		SCALE	DRAWING NO.	DATE
		1:1	GAM-447	6/5/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[ASVFSVF14K254](#)