

Detailed Specifications

| | |
|------------------------------------|-------------------------------|
| Frame Width: | 30[mm] |
| Frame Height: | 30[mm] |
| Frame Depth: | 10[mm] |
| Max. Air Flow: | 3.9[CFM] |
| Max. Air Flow: | 0.11[m ³ per min] |
| Max. Static Pressure: | 0.19[In H ₂ O] |
| Max. Static Pressure: | 48[Pa] |
| Fan Speed: | 9500[RPM] |
| Noise: | 30[dB] |
| Life Expectancy: | 40 degree C 30,000 Hours[L10] |
| Bearing Type: | Sleeve Bearing |
| Nominal Voltage: | 12[V] |
| Operating Voltage - Lower: | 7[V] |
| Operating Voltage - Upper: | 13.2[V] |
| Current: | 0.07[A] |
| Input Power: | 0.8[W] |
| Mass: | 8.5[g] |
| Tach / Locked Rotor Output: | Locked Rotor |
| Status: | Active |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[03010SS-12M-AL-00](#)