

Detailed Specifications

Frame Width:	30[mm]
Frame Height:	30[mm]
Frame Depth:	10[mm]
Max. Air Flow:	3.9[CFM]
Max. Air Flow:	0.11[m ³ per min]
Max. Static Pressure:	0.19[In H ₂ O]
Max. Static Pressure:	48[Pa]
Fan Speed:	9500[RPM]
Noise:	30[dB]
Life Expectancy:	40 degree C 30,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.07[A]
Input Power:	0.8[W]
Mass:	8.5[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[03010SS-12M-AT-00](#)