

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	10[mm]
Max. Air Flow:	4.9[CFM]
Max. Air Flow:	0.14[m ³ per min]
Max. Static Pressure:	0.11[In H ₂ O]
Max. Static Pressure:	27.5[Pa]
Fan Speed:	5500[RPM]
Noise:	21[dB]
Life Expectancy:	40 degree C 30,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	5[V]
Operating Voltage - Lower:	4.5[V]
Operating Voltage - Upper:	5.5[V]
Current:	0.09[A]
Input Power:	0.5[W]
Mass:	16[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04010SS-05L-AT-00](#)