

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	15[mm]
Max. Air Flow:	26.8[CFM]
Max. Air Flow:	0.76[m ³ per min]
Max. Static Pressure:	0.09[In H ₂ O]
Max. Static Pressure:	23.5[Pa]
Fan Speed:	2500[RPM]
Noise:	27.5[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	12[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.07[A]
Input Power:	1.7[W]
Mass:	55[g]
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08015SS-24L-AA-00](#)