

Detailed Specifications

| | |
|------------------------------------|-------------------------------|
| Frame Width: | 80[mm] |
| Frame Height: | 80[mm] |
| Frame Depth: | 15[mm] |
| Max. Air Flow: | 33.9[CFM] |
| Max. Air Flow: | 0.96[m ³ per min] |
| Max. Static Pressure: | 0.14[In H ₂ O] |
| Max. Static Pressure: | 34.2[Pa] |
| Fan Speed: | 3100[RPM] |
| Noise: | 34[dB] |
| Life Expectancy: | 40 degree C 40,000 Hours[L10] |
| Bearing Type: | Sleeve Bearing |
| Nominal Voltage: | 24[V] |
| Operating Voltage - Lower: | 12[V] |
| Operating Voltage - Upper: | 26.4[V] |
| Current: | 0.12[A] |
| Input Power: | 2.9[W] |
| Mass: | 55[g] |
| Tach / Locked Rotor Output: | Tach Output |
| Status: | Active |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08015SS-24N-AT-00](#)