

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Max. Air Flow:	28.2[CFM]
Max. Air Flow:	0.79[m ³ per min]
Max. Static Pressure:	0.08[In H ₂ O]
Max. Static Pressure:	21.6[Pa]
Fan Speed:	2400[RPM]
Noise:	25[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.11[A]
Input Power:	1.32[W]
Mass:	94.8[g]
Tach / Locked Rotor Output:	No
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08025KA-12K-AA-00](#)