

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Max. Air Flow:	35.3[CFM]
Max. Air Flow:	0.988[m3 per min]
Max. Static Pressure:	0.13[In H2O]
Max. Static Pressure:	32.3[Pa]
Fan Speed:	3000[RPM]
Noise:	31[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.2[A]
Input Power:	2.4[W]
Mass:	94.8[g]
Tach / Locked Rotor Output:	No
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08025KA-12M-EA-00](#)