

Detailed Specifications

| | |
|------------------------------------|------------------------------|
| Frame Width: | 80[mm] |
| Frame Height: | 80[mm] |
| Frame Depth: | 25[mm] |
| Max. Air Flow: | 40.2[CFM] |
| Max. Air Flow: | 1.13[m ³ per min] |
| Max. Static Pressure: | 0.16[In H ₂ O] |
| Max. Static Pressure: | 40.2[Pa] |
| Fan Speed: | 3400[RPM] |
| Noise: | 35[dB] |
| Bearing Type: | Ball Bearing |
| Nominal Voltage: | 12[V] |
| Operating Voltage - Lower: | 6[V] |
| Operating Voltage - Upper: | 13.8[V] |
| Current: | 0.26[A] |
| Input Power: | 3.12[W] |
| Mass: | 94.8[g] |
| Tach / Locked Rotor Output: | Tach Output |
| Status: | EOL |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08025KA-12P-AT-00](#)