

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Max. Air Flow:	24.7[CFM]
Max. Air Flow:	0.692[m3 per min]
Max. Static Pressure:	0.07[In H2O]
Max. Static Pressure:	16.7[Pa]
Fan Speed:	2150[RPM]
Noise:	22[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.06[A]
Input Power:	1.44[W]
Mass:	94.8[g]
Tach / Locked Rotor Output:	No
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08025KA-24J-EA-00](#)