

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Max. Air Flow:	41.3[CFM]
Max. Air Flow:	1.17[m ³ per min]
Max. Static Pressure:	0.15[In H ₂ O]
Max. Static Pressure:	37.5[Pa]
Fan Speed:	3100[RPM]
Noise:	30[dB]
Life Expectancy:	60 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	12[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.08[A]
Input Power:	1.9[W]
Mass:	80[g]
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08025SA-24N-EA-D0](#)