

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	40.6[CFM]
Max. Air Flow:	1.14[m ³ per min]
Max. Static Pressure:	0.11[In H ₂ O]
Max. Static Pressure:	27[Pa]
Fan Speed:	2450[RPM]
Noise:	34[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.16[A]
Input Power:	1.92[W]
Mass:	94.8[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09225KA-12L-AL-00](#)