

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	47.6[CFM]
Max. Air Flow:	1.33[m ³ per min]
Max. Static Pressure:	0.15[In H ₂ O]
Max. Static Pressure:	37.2[Pa]
Fan Speed:	2850[RPM]
Noise:	37.5[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.22[A]
Input Power:	2.6[W]
Mass:	94.8[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09225KA-12M-AL-00](#)