

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	26.5[CFM]
Max. Air Flow:	0.742[m3 per min]
Max. Static Pressure:	0.06[In H2O]
Max. Static Pressure:	14.2[Pa]
Fan Speed:	1750[RPM]
Noise:	25[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.05[A]
Input Power:	1.2[W]
Mass:	94.8[g]
Tach / Locked Rotor Output:	No
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09225KA-24J-AA-00](#)