

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	25[mm]
<b>Max. Air Flow:</b>	47.6[CFM]
<b>Max. Air Flow:</b>	1.33[m <sup>3</sup> per min]
<b>Max. Static Pressure:</b>	0.15[In H <sub>2</sub> O]
<b>Max. Static Pressure:</b>	37.2[Pa]
<b>Fan Speed:</b>	2850[RPM]
<b>Noise:</b>	37.5[dB]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage - Lower:</b>	10[V]
<b>Operating Voltage - Upper:</b>	27.6[V]
<b>Current:</b>	0.12[A]
<b>Input Power:</b>	2.88[W]
<b>Mass:</b>	94.8[g]
<b>Tach / Locked Rotor Output:</b>	No
<b>Status:</b>	EOL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09225KA-24M-AA-00](#)