

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	25[mm]
<b>Max. Air Flow:</b>	96.4[CFM]
<b>Max. Air Flow:</b>	2.73[m3 per min]
<b>Max. Static Pressure:</b>	0.6[In H2O]
<b>Max. Static Pressure:</b>	150[Pa]
<b>Fan Speed:</b>	5600[RPM]
<b>Noise:</b>	51[dB]
<b>Life Expectancy:</b>	25 degree C 100,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	12[V]
<b>Operating Voltage - Lower:</b>	7[V]
<b>Operating Voltage - Upper:</b>	13.8[V]
<b>Current:</b>	0.72[A]
<b>Input Power:</b>	8.6[W]
<b>Mass:</b>	150[g]
<b>IP Rating:</b>	IP68/IP69K
<b>Tach / Locked Rotor Output:</b>	No
<b>Status:</b>	Active

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09225VA-12Q-CA-00](#)