

## Detailed Specifications

|                                    |                                |
|------------------------------------|--------------------------------|
| <b>Frame Width:</b>                | 92[mm]                         |
| <b>Frame Height:</b>               | 92[mm]                         |
| <b>Frame Depth:</b>                | 38[mm]                         |
| <b>Max. Air Flow:</b>              | 103.8[CFM]                     |
| <b>Max. Air Flow:</b>              | 2.94[m3 per min]               |
| <b>Max. Static Pressure:</b>       | 0.57[In H2O]                   |
| <b>Max. Static Pressure:</b>       | 142[Pa]                        |
| <b>Fan Speed:</b>                  | 5000[RPM]                      |
| <b>Noise:</b>                      | 52.5[dB]                       |
| <b>Life Expectancy:</b>            | 25 degree C 100,000 Hours[L10] |
| <b>Bearing Type:</b>               | Ball Bearing                   |
| <b>Nominal Voltage:</b>            | 12[V]                          |
| <b>Operating Voltage - Lower:</b>  | 7[V]                           |
| <b>Operating Voltage - Upper:</b>  | 13.8[V]                        |
| <b>Current:</b>                    | 0.8[A]                         |
| <b>Input Power:</b>                | 9.6[W]                         |
| <b>Mass:</b>                       | 230[g]                         |
| <b>Tach / Locked Rotor Output:</b> | No                             |
| <b>Status:</b>                     | PCN                            |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09238RA-12L-EA-00](#)