

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	38[mm]
Max. Air Flow:	129.9[CFM]
Max. Air Flow:	3.68[m3 per min]
Max. Static Pressure:	0.89[In H2O]
Max. Static Pressure:	222[Pa]
Fan Speed:	6200[RPM]
Noise:	59[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	14[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.71[A]
Input Power:	17[W]
Mass:	230[g]
Tach / Locked Rotor Output:	No
Status:	PCN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09238RA-24N-EA-00](#)