

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	38[mm]
<b>Max. Air Flow:</b>	152.5[CFM]
<b>Max. Air Flow:</b>	4.32[m3 per min]
<b>Max. Static Pressure:</b>	1.2[In H2O]
<b>Max. Static Pressure:</b>	300[Pa]
<b>Fan Speed:</b>	7200[RPM]
<b>Noise:</b>	62.5[dB]
<b>Life Expectancy:</b>	25 degree C 100,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage - Lower:</b>	14[V]
<b>Operating Voltage - Upper:</b>	26.4[V]
<b>Current:</b>	1.13[A]
<b>Input Power:</b>	27.1[W]
<b>Mass:</b>	230[g]
<b>Tach / Locked Rotor Output:</b>	No
<b>Status:</b>	PCN

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09238RA-24Q-EA-00](#)