

Detailed Specifications

Frame Width:	120[mm]
Frame Height:	120[mm]
Frame Depth:	38[mm]
Max. Air Flow:	186[CFM]
Max. Air Flow:	5.25[m ³ per min]
Max. Static Pressure:	3[In H ₂ O]
Max. Static Pressure:	740[Pa]
Fan Speed:	9000[RPM]
Noise:	72[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	48[V]
Operating Voltage - Lower:	38[V]
Operating Voltage - Upper:	60[V]
Current:	0.82[A]
Input Power:	39.4[W]
Mass:	580[g]
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[12038MA-48R-EE-00](#)