

Detailed Specifications

Frame Width:	120[mm]
Frame Height:	120[mm]
Frame Depth:	38[mm]
Max. Air Flow:	243.6[CFM]
Max. Air Flow:	6.9[m3 per min]
Max. Static Pressure:	1.49[In H2O]
Max. Static Pressure:	370[Pa]
Fan Speed:	6400[RPM]
Noise:	66[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	18[V]
Operating Voltage - Upper:	27.6[V]
Current:	1.48[A]
Input Power:	35.5[W]
Mass:	370[g]
IP Rating:	IP68/IP69K
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[12038VA-24R-GA-00](#)