

Detailed Specifications

Frame Size:	145[mm]
Frame Width:	39[mm]
Nominal Voltage:	12[V]
Max. Air Flow:	51.2[CFM]
Max. Static Pressure:	1.55[In H2O]
Speed:	2450[min^{-1}]
Noise:	54.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	8[V]
Operating Voltage Upper:	13.2[V]
Nominal Current:	1.25[A]
Input Power:	15[W]
Mass:	390[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[14539GA-12N-AA-00](#)