

## Detailed Specifications

<b>Frame Width:</b>	60[mm]
<b>Frame Height:</b>	60[mm]
<b>Frame Depth:</b>	20[mm]
<b>Max. Air Flow:</b>	14.8[CFM]
<b>Max. Air Flow:</b>	0.42[m3 per min]
<b>Max. Static Pressure:</b>	0.11[In H2O]
<b>Max. Static Pressure:</b>	28.7[Pa]
<b>Fan Speed:</b>	3600[RPM]
<b>Noise:</b>	27[dB]
<b>Life Expectancy:</b>	60 degree C 40,000 Hours AA/EA[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage - Lower:</b>	15[V]
<b>Operating Voltage - Upper:</b>	27.6[V]
<b>Current:</b>	0.045[A]
<b>Input Power:</b>	1.1[W]
<b>Mass:</b>	85[g]
<b>Tach / Locked Rotor Output:</b>	Tach Output

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[2408NL-05W-B39-L50](#)