

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	37[CFM]
Max. Air Flow:	1.05[m3 per min]
Max. Static Pressure:	0.57[In H2O]
Max. Static Pressure:	142.5[Pa]
Fan Speed:	7800[RPM]
Noise:	46[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.52[A]
Input Power:	6.2[W]
Mass:	65[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[2410ML-04W-B89-E00](#)