

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	33.1[CFM]
Max. Air Flow:	0.94[m3 per min]
Max. Static Pressure:	0.5[In H2O]
Max. Static Pressure:	125[Pa]
Fan Speed:	6800[RPM]
Noise:	45[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	25.2[V]
Current:	0.19[A]
Input Power:	4.6[W]
Mass:	65[g]
Tach / Locked Rotor Output:	No
Status:	EOL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[2410ML-05W-B70-B00](#)