

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	25[mm]
<b>Max. Air Flow:</b>	61.1[CFM]
<b>Max. Air Flow:</b>	1.73[m3 per min]
<b>Max. Static Pressure:</b>	0.26[In H2O]
<b>Max. Static Pressure:</b>	65[Pa]
<b>Fan Speed:</b>	3600[RPM]
<b>Noise:</b>	38.5[dB]
<b>Life Expectancy:</b>	60 degree C 40,000 Hours AA/EA[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage 0 Lower:</b>	14[V]
<b>Operating Voltage 0 Upper:</b>	27.6[V]
<b>Current:</b>	0.14[A]
<b>Input Power:</b>	3.4[W]
<b>Mass:</b>	135[g]
<b>Tach / Locked Rotor Output:</b>	Tach Output

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610VL-05W-B39-E50](#)