

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	32[mm]
<b>Max. Air Flow:</b>	47.3[CFM]
<b>Max. Air Flow:</b>	1.34[m3 per min]
<b>Max. Static Pressure:</b>	0.16[In H2O]
<b>Max. Static Pressure:</b>	41[Pa]
<b>Fan Speed:</b>	2600[RPM]
<b>Noise:</b>	34[dB]
<b>Life Expectancy:</b>	25 degree C 100,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	12[V]
<b>Operating Voltage 0 Lower:</b>	6[V]
<b>Operating Voltage 0 Upper:</b>	13.8[V]
<b>Current:</b>	0.21[A]
<b>Input Power:</b>	2.5[W]
<b>Mass:</b>	230[g]
<b>Tach / Locked Rotor Output:</b>	No

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3612KL-04W-B30-B00](#)