

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	32[mm]
Max. Air Flow:	47.3[CFM]
Max. Air Flow:	1.34[m ³ per min]
Max. Static Pressure:	0.16[In H ₂ O]
Max. Static Pressure:	41[Pa]
Fan Speed:	2600[RPM]
Noise:	34[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.21[A]
Input Power:	2.5[W]
Mass:	230[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3612KL-04W-B30-E00](#)