

## Detailed Specifications

<b>Frame Width:</b>	119[mm]
<b>Frame Height:</b>	119[mm]
<b>Frame Depth:</b>	25[mm]
<b>Max. Air Flow:</b>	63.5[CFM]
<b>Max. Air Flow:</b>	1.8[m3 per min]
<b>Max. Static Pressure:</b>	0.07[In H2O]
<b>Max. Static Pressure:</b>	17.9[Pa]
<b>Fan Speed:</b>	1600[RPM]
<b>Noise:</b>	27[dB]
<b>Life Expectancy:</b>	25 degree C 100,000 Hours (B00 / E00) [L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage 0 Lower:</b>	10[V]
<b>Operating Voltage 0 Upper:</b>	27.6[V]
<b>Current:</b>	0.08[A]
<b>Input Power:</b>	1.9[W]
<b>Mass:</b>	180[g]
<b>Tach / Locked Rotor Output:</b>	No

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4710KL-05W-B10-B00](#)