

Detailed Specifications

| | |
|------------------------------------|---|
| Frame Width: | 119[mm] |
| Frame Height: | 119[mm] |
| Frame Depth: | 25[mm] |
| Max. Air Flow: | 63.5[CFM] |
| Max. Air Flow: | 1.8[m3 per min] |
| Max. Static Pressure: | 0.07[In H2O] |
| Max. Static Pressure: | 17.9[Pa] |
| Fan Speed: | 1600[RPM] |
| Noise: | 27[dB] |
| Life Expectancy: | 25 degree C 100,000 Hours (B00 / E00) [L10] |
| Bearing Type: | Ball Bearing |
| Nominal Voltage: | 24[V] |
| Operating Voltage 0 Lower: | 10[V] |
| Operating Voltage 0 Upper: | 27.6[V] |
| Current: | 0.08[A] |
| Input Power: | 1.9[W] |
| Mass: | 180[g] |
| Tach / Locked Rotor Output: | Locked Rotor |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4710KL-05W-B19-B00](#)