

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	25[mm]
Max. Air Flow:	100.6[CFM]
Max. Air Flow:	2.85[m3 per min]
Max. Static Pressure:	0.16[In H2O]
Max. Static Pressure:	41.9[Pa]
Fan Speed:	2500[RPM]
Noise:	38.5[dB]
Life Expectancy:	25 degree C 100,000 Hours (B00 / E00) [L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	10[V]
Operating Voltage 0 Upper:	27.6[V]
Current:	0.22[A]
Input Power:	5.3[W]
Mass:	180[g]
Tach / Locked Rotor Output:	No

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4710KL-05W-B40-B00](#)