

Detailed Specifications

Frame Size:	280[mm]
Frame Depth:	129[mm]
Nominal Voltage:	24[V]
Max. Air Flow:	940[CFM]
Max. Static Pressure:	1.3[In H2O]
Speed:	1700[rpm]
Noise:	70[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage - Lower:	18[V]
Operating Voltage - Upper:	30[V]
Nominal Current:	3.8[A]
Input Power:	91.2[W]
Mass:	2100[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[F280A4-113-D0510](#)