

Detailed Specifications

Frame Width:	150[mm]
Frame Height:	172[mm]
Frame Depth:	51[mm]
Max. Air Flow:	473[CFM]
Max. Air Flow:	13.4[m ³ per min]
Max. Static Pressure:	3.204[In H ₂ O]
Max. Static Pressure:	798[Pa]
Fan Speed:	6500[RPM]
Noise:	73[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	18[V]
Operating Voltage 0 Upper:	28[V]
Current:	4[A]
Input Power:	96[W]
Mass:	800[g]
IP Rating:	Non IP model
Tach / Locked Rotor Output:	Tach Output

PWM Speed Control Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[R150H1-051-D0560](#)