

**EP 2 SAKG46/35 HP/TF/GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |                                     |
|------------|-------------------------------------|
| Version    | SAK Series, End plate, yellow, 2 mm |
| Order No.  | <a href="#">0180800000</a>          |
| Type       | EP 2 SAKG46/35 HP/TF/GE             |
| GTIN (EAN) | 4008 190006938                      |
| Qty.       | 10 pc(s).                           |

## EP 2 SAKG46/35 HP/TF/GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 91 mm  | Depth (inches)  | 3.583 inch |
| Height     | 160 mm | Height (inches) | 6.299 inch |
| Width      | 2 mm   | Width (inches)  | 0.079 inch |
| Net weight | 33.4 g |                 |            |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C         |                                  |        |

## Environmental Product Compliance

|            |                |      |                                 |
|------------|----------------|------|---------------------------------|
| REACH SVHC | Lead 7439-92-1 | SCIP | 8689236b-1c04-4b82-9d8d-177abb5 |
|------------|----------------|------|---------------------------------|

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-2   |        |        |

## System specifications

|         |                            |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

## Additional technical data

|         |    |
|---------|----|
| Snap-on | No |
|---------|----|

## Dimensions

|              |       |
|--------------|-------|
| TS 32 offset | 80 mm |
|--------------|-------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ECLASS 9.0  | 27-14-11-33 |
| ECLASS 9.1  | 27-14-11-33 | ECLASS 10.0 | 27-14-11-33 |
| ECLASS 11.0 | 27-14-11-33 | ECLASS 12.0 | 27-14-11-33 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>                    |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0180800000](#)