

KSG M25 BS O SC 2 G25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



The KSG is only intended for use when connecting non-armoured cables and lines. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -35°C to $+90^{\circ}\text{C}$. When using a silicone seal, a temperature range of -60°C to $+180^{\circ}\text{C}$ is possible. The O-ring and the cable gland included in the delivery are made from the same material. IP66 or IP68 protection at a depth of 25 metres under water (a pressure of 2.5 bar) is guaranteed when using this sealing material. The KSG is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e.

General ordering data

Version	KSG (Klippon standard Ex cable gland), Cable glands, straight, M 25, 16 mm, OD min. 13.5 - OD max. 20 mm, IP66, IP68 - 2.5 bar, Brass
Order No.	0930511212
Type	KSG M25 BS O SC 2 G25
GTIN (EAN)	4032248918102
Qty.	20 pc(s).

Creation date January 16, 2022 10:26:12 PM CET

Catalogue status 17.12.2021 / We reserve the right to make technical changes.

KSG M25 BS O SC 2 G25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	33 mm	Length (inches)	1.299 inch
Net weight	168.3 g		

Temperatures

Operating temperature	-60 °C... 180 °C
-----------------------	------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Certificate numbers cable gland

Approval conditions	ATEX, IECEX, EAC	Certificate No. (ATEX)	SIRA05ATEX1287X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate no. cable gland (EAC)	RU C-DE.HA65.B.00568 20
Identification	ATEX: II 2GD, Ex db IIC Gb, Ex ta IIIC Da and/or II 2 GD, Ex eb IIC Gb, Ex ta IIIC Da, IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da		

General information

AF size 1	38 mm	Cable glands	metric, brass
Explosion protection type	Pressure-resistant Ex d encapsulation, Improved safety Ex e	External thread	M 25
Installation guidelines	See assembly instructions	Length of thread	16 mm
Material	Brass	O-Ring	Silicone
Operating temperature range, max.	180 °C	Operating temperature range, min.	-60 °C
Outer cable diameter, max.	20 mm	Outer cable diameter, min.	13.5 mm
Pitch of thread	1.5 mm	Protection degree	IP66, IP68 - 2.5 bar
Protection degree with GWDR	IP66, IP68 - 2.5 bar	Seal insert	Silicone
Sealing	Silicone	Size of protective cap	L38
Water depth	25 m (30 Min.)		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-34	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



Approvals	EAC; ATEX; IECEX
ROHS	Conform

Creation date January 16, 2022 10:26:12 PM CET

Catalogue status 17.12.2021 / We reserve the right to make technical changes.

2

KSG M25 BS O SC 2 G25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

Approval/Certificate/Document of Conformity	IECEXSIR05.0067X SIRA05ATEX1287X EU Declaration of Conformity - Klippon KSG cable Gland - DoC DE PS2680 160315 004ISS01
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	Assembly guidelines
Catalogues	Catalogues in PDF-format
Brochures	MB OVERV. PROCESS WD DE MB PROCESS EN PI KLIPPON CABLE GL EN PI KLIPPON CABLE GL EN

KSG M25 BS O SC 2 G25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Nylon flat gasket - KSWN



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M25	Version
Order No.	1076640000	KSWN (flat gasket - nylon), Sealing ring, M 25, Nylon 6
GTIN (EAN)	4032248838684	
Qty.	25 pc(s).	

Safety serrated washer



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SZS M25	Version
Order No.	1736320000	SZS (serrated washer), Retaining toothed washers, M 25, Stainless steel 1.4404 (316L)
GTIN (EAN)	4008190963521	
Qty.	10 pc(s).	

KSG M25 BS O SC 2 G25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**Earth tags**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	EA-RING MS/M25 SC	Version
Order No.	0930710003	EA (earthing rings), Earthing ring, M 25, Brass
GTIN (EAN)	4032248976188	
Qty.	20 pc(s).	

Vulcanised fibre gasket - KSWF

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWF M25	Version
Order No.	0899770000	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 25, Vulcanized
GTIN (EAN)	4032248850167	fibre
Qty.	25 pc(s).	

KSG M25 BS O SC 2 G25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Brass lock nuts, natural finish**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M25 MS SC	Version
Order No.	0930640003	SKMU MS (brass locknut), Locknut, M 25, 4 mm, Brass
GTIN (EAN)	4032248976072	
Qty.	25 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0930511212](#)