

CUTFIX 8 INTERFACE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- For automatically cutting individual wires to length
- High repeat accuracy due to the precise servo DC drive
- Interface for controlling the automatic cutter via an IBM-compatible PC

General ordering data

Version	Cutting machine
Order No.	2580010000
Type	CUTFIX 8 INTERFACE
GTIN (EAN)	4050118605839
Qty.	1 pc(s).
Replacement parts	9054740000

Creation date October 11, 2022 7:59:31 PM CEST

Catalogue status 07.10.2022 / We reserve the right to make technical changes.

CUTFIX 8 INTERFACE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	360 mm	Depth (inches)	14.173 inch
Height	470 mm	Height (inches)	18.504 inch
Width	380 mm	Width (inches)	14.961 inch
Net weight	20,809 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Automatic cutting

Amount pre-selection, max.	Adjustable part quantity code	Aperture (max. diameter)	8 mm outer diameter
Correction for length	Slip correction in mm can be programmed to suit the part.	Display	LCD display
Drive	electrical	Electrical connection	100 - 240 V / 50 Hz / 240 VA
Feeding speed, max.	1.5 m/s	Flexible/solid individual conductors	max. 10 mm ² / max. 2.5 mm ²
Interface	USB 1.1, USB 2.0	Keyboard	Touch display
Length pre-selection, max.	999,999 mm	Length pre-selection, min.	2 mm
Software	for data exchanging with IBM-compatible PC, Integrated interface to read CAE data	Storage	Up to 2,000 cutting jobs

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ECLASS 9.0	17-13-01-01
ECLASS 9.1	17-13-01-03	ECLASS 10.0	17-13-01-03
ECLASS 11.0	17-13-01-01	ECLASS 12.0	17-13-01-01

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2580010000](#)