

**WQV 6/5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	W-Series, Cross-connector, For the terminals, Number of poles: 5
Order No.	<a href="#">1062660000</a>
Type	WQV 6/5
GTIN (EAN)	4008190176914
Qty.	50 pc(s).

Creation date January 20, 2022 2:14:21 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## WQV 6/5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	37.8 mm	Height (inches)	1.488 inch
Width	7.6 mm	Width (inches)	0.299 inch
Net weight	8.2 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

## Cross-connector

Number of cross-connected terminals	5	Rated current, multi-pole	57 A
Tightening torque range for fixing screw	0.5... 1.0 Nm	Type	Cross-connector

## Dimensions

Pitch in mm (P)	8 mm
-----------------	------

## General

Installation advice	Direct mounting	Number of poles	5
---------------------	-----------------	-----------------	---

## Rating data

Rated current	57 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40		

## Approvals

Approvals



ROHS Conform

Creation date January 20, 2022 2:14:21 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

**WQV 6/5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Beipackzettel_WQV.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**Data sheet****WQV 6/5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Cutting and notching tools for cross-connections**

- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

**General ordering data**

Type	WAW 1 NEUTRAL	Version
Order No.	<a href="#">9004500000</a>	Miscellaneous tools
GTIN (EAN)	4008190053925	
Qty.	1 pc(s).	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1062660000](#)