

**STB 21.6/IH/SW WTL6/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Accessories, Socket        |
| Order No.  | <a href="#">1071040000</a> |
| Type       | STB 21.6/IH/SW WTL6/3      |
| GTIN (EAN) | 4008190859985              |
| Qty.       | 50 pc(s).                  |

Creation date January 20, 2022 6:42:12 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## STB 21.6/IH/SW WTL6/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 26.6 mm | Depth (inches)  | 1.047 inch |
| Height     | 6.1 mm  | Height (inches) | 0.24 inch  |
| Width      | 6.1 mm  | Width (inches)  | 0.24 inch  |
| Net weight | 2.34 g  |                 |            |

## Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |
|----------------------------------|--------|----------------------------------|--------|

## Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

## Material data

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | Wemid | Colour | black |
| UL 94 flammability rating | V-0   |        |       |

## System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

## Additional technical data

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in | Type of mounting    | when screwed in |

## Dimensions

|                                     |         |               |         |
|-------------------------------------|---------|---------------|---------|
| Metric size of the thread, external | 0 M3.0  | Plug-in depth | 11.1 mm |
| TS 32 offset                        | 54.5 mm |               |         |

## General

|                     |                 |                                   |        |
|---------------------|-----------------|-----------------------------------|--------|
| Installation advice | Direct mounting | Operating temperature range, max. | 100 °C |
|---------------------|-----------------|-----------------------------------|--------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 |             |             |

## Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**STB 21.6/IH/SW WTL6/3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">EAC certificate</a>                 |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                 |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>        |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>        |
| Brochures                                   |   |

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1071040000](#)