

PAC-UNIV-HE50-HE50-3M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Version	Pre-assembled cable, PAC
Order No.	1349720030
Type	PAC-UNIV-HE50-HE50-3M
GTIN (EAN)	4032248217632
Qty.	1 pc(s).

Creation date January 23, 2022 4:28:08 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

PAC-UNIV-HE50-HE50-3M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 512.7 g

Temperatures

Storage temperature -10...60 °C Operating temperature -10...50 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

General Data

Cable	Cable LiYY	Cable length	3 m
Connector PLC side	HE10 50 P	Interface connector	HE10 50 P
Material	PVC	Number of poles, min.	50-pole
Outer diameter	13.4 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm ²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20		

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1349720030](#)