

**IE-CC-NM-SMAM-2M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

**Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Antenna cable, Connection 1:; N-type male, Connection 2:; SMA plug, Length: 2 m
Order No.	<a href="#">1491180000</a>
Type	IE-CC-NM-SMAM-2M
GTIN (EAN)	4050118300741
Qty.	1 pc(s).

Creation date January 26, 2022 4:06:02 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

**IE-CC-NM-SMAM-2M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Length	2 m	Length (inches)	78.74 inch
Net weight	120 g		

**Temperatures**

Storage temperature	-70 °C...85 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Electrical properties of cable**

Attenuation at 2000 MHz	approx. 0.5 dB/m	Attenuation at 800 MHz	approx. 0.31 dB/m
Characteristic impedance	50 Ω		

**Mechanical and material properties of cable**

Material sheath	Polyethylene	Min. bending radius, once only	12,7 mm
Min. bending radius, repetitive	50,8 mm	Sheath diameter	4.95 mm
UV-resistant	Yes		

**Technical data**

Type of connection	Connection 1:, N-type male, Connection 2:, SMA plug
--------------------	-----------------------------------------------------

**Environmental conditions**

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-70 °C

**Classifications**

ETIM 6.0	EC001682	ETIM 7.0	EC001682
ETIM 8.0	EC001682	ECLASS 9.0	27-06-03-10
ECLASS 9.1	27-06-03-10	ECLASS 10.0	27-06-03-10
ECLASS 11.0	27-06-03-10		

**Approvals**

Approvals



ROHS

Conform

**Downloads**Catalogues [Catalogues in PDF-format](#)

Brochures

**IE-CC-NM-SMAM-2M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

Product image



Connection 1: SMA male

Product image



Connection 2: N-type male

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1491180000](#)