

## CLI C 2-4 OR/SW 3 CD


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, orange
Order No.	<a href="#">1568261512</a>
Type	CLI C 2-4 OR/SW 3 CD
GTIN (EAN)	4008 1909 16220
Qty.	250 pc(s).

Creation date January 26, 2022 9:26:36 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## CLI C 2-4 OR/SW 3 CD

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	8 mm	Depth (inches)	0.315 inch
Height	4 mm	Height (inches)	0.157 inch
Width	7 mm	Width (inches)	0.276 inch
Net weight	0.209 g		

### Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

### General data

Colour	orange	Colour of printing	black
Halogen	Yes	Insulation cross-section, max.	10
Material	PVC, soft, without Cadmium	Material colour according to resistance code	3
Number of markers per combination	1 Reel = Conductor and cable markers	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Numbers
Printing	3	Printing method	hot-embossing
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0	Version	CD
Width	7 mm		

### Conductor and cable markers

Conductor O.D.	4 - 10 mm	Conductor O.D., max.	10 mm
Conductor O.D., min.	4 mm	Conductor cross-section, max.	16 mm <sup>2</sup>
Conductor cross-section, min.	2.5 mm <sup>2</sup>	Cross-section for connected wire	2.5 - 16 mm <sup>2</sup>
Halogen	Yes		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN, WSCAD</a>
Product Change Notification	<a href="#">PCN CableLine_DE</a> <a href="#">PCN CableLine_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**CLI C 2-4 OR/SW 3 CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Similar to illustration

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1568261512](#)