

CLI C 2-4 GE/SW S CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|---|
| Version | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, yellow |
| Order No. | 1568261673 |
| Type | CLI C 2-4 GE/SW S CD |
| GTIN (EAN) | 4008 190094331 |
| Qty. | 250 pc(s). |

Creation date January 26, 2022 9:36:48 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

CLI C 2-4 GE/SW S CD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 8 mm | Depth (inches) | 0.315 inch |
| Height | 4 mm | Height (inches) | 0.157 inch |
| Width | 7 mm | Width (inches) | 0.276 inch |
| Net weight | 0.214 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|--------------------------------------|--|--------------------|
| Colour | yellow | Colour of printing | black |
| Halogen | Yes | Insulation cross-section, max. | 10 |
| Material | PVC, soft, without Cadmium | Material colour according to resistance code | 4 |
| Number of markers per combination | 1 Reel = Conductor and cable markers | Operating temperature range | -30...80 °C |
| Operating temperature range, max. | 80 °C | Operating temperature range, min. | -30 °C |
| Orientation of print | horizontal | Printed characters | Upper-case letters |
| Printing | S | Printing method | hot-embossing |
| Recommended industries | Process, Machinery | Type of printing | Standard |
| UL 94 flammability rating | V-0 | Version | CD |
| Width | 7 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor O.D. | 4 - 10 mm | Conductor O.D., max. | 10 mm |
| Conductor O.D., min. | 4 mm | Conductor cross-section, max. | 16 mm ² |
| Conductor cross-section, min. | 2.5 mm ² | Cross-section for connected wire | 2.5 - 16 mm ² |
| Halogen | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|-----------------------------|--|
| Engineering Data | EPLAN, WSCAD |
| Product Change Notification | PCN CableLine_DE PCN CableLine_EN |
| Catalogues | Catalogues in PDF-format |

CLI C 2-4 GE/SW S CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Similar to illustration

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1568261673](#)