

**KV 16-M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	VG H (HDC halved cable gland), Cable glands, PG 16, IP65, Brass, nickel-plated
Order No.	<a href="#">1656410000</a>
Type	KV 16-M
GTIN (EAN)	4008 190409425
Qty.	10 pc(s).

Creation date January 27, 2022 3:07:32 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

**KV 16-M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 13.9 g

**Temperatures**

Operating temperature -20 °C...60 °C

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**General information**

AF size 1	10 mm	Cable glands	PG
External thread	PG 16	Material	Brass, nickel-plated
Notch multi-layer sealing diameter 1	7.5 mm	Notch multi-layer sealing diameter 2	10 mm
Notch multi-layer sealing diameter 3	12.5 mm	Notch multi-layer sealing diameter 4	15 mm
O-Ring	NBR	Operating temperature range, max.	60 °C
Operating temperature range, min.	-20 °C	Protection degree	IP65
Protection degree with GWDR	IP65		

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

**Approvals**

ROHS Conform

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1656410000](#)