

**GWDR PG13,5-PO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

|            |   |
|------------|---|
| Version    | GWDR PO (flat gasket - polyethylene), Sealing ring, PG 13.5, Polyethylene |
| Order No.  | <a href="#">1719470000</a>  |
| Type       | GWDR PG13,5-PO  |
| GTIN (EAN) | 4008 19035272 1   |
| Qty.       | 100 pc(s).  |

Creation date January 27, 2022 8:46:18 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## GWDR PG13,5-PO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 0.27 g

### Temperatures

Operating temperature -30 °C...90 °C

### General information

|                                   |              |                                   |         |
|-----------------------------------|--------------|-----------------------------------|---------|
| Cable glands                      | PG           | Diameter of sealing ring          | 25 mm   |
| External thread                   | PG 13.5      | Inside diameter D2                | 20.4 mm |
| Material                          | Polyethylene | O.D.                              | 25 mm   |
| Operating temperature range, max. | 90 °C        | Operating temperature range, min. | -30 °C  |
| Sealing                           | PE-HD        | Thickness                         | 2 mm    |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001181    | ETIM 7.0    | EC001181    |
| ETIM 8.0    | EC001181    | ECLASS 9.0  | 27-43-03-19 |
| ECLASS 9.1  | 27-14-44-90 | ECLASS 10.0 | 27-43-03-19 |
| ECLASS 11.0 | 27-43-03-19 |             |             |

### Approvals

ROHS Conform

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">EPLAN, WSCAD</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |

**Data sheet**

**GWDR PG13,5-PO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1719470000](#)