

GWDR PG7-NP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR NP (flat gasket - neoprene), Sealing ring, PG 7, Neoprene
Order No.	1719540000
Type	GWDR PG7-NP
GTIN (EAN)	4008 190352806
Qty.	100 pc(s).

Creation date January 27, 2022 8:53:04 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

GWDR PG7-NP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.25 g

Temperatures

Operating temperature -40 °C... 100 °C

General information

Cable glands	PG	Diameter of sealing ring	17 mm
External thread	PG 7	Inside diameter D2	11.6 mm
Material	Neoprene	O.D.	17 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Thickness	1.2 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19		

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

GWDR PG7-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1719540000](#)