

ADAP EX 3/4NPT-M32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

Version	ADAP (adaptor, extensions and reductions), Adapter, 3/4" NPT ,M 32, IP54, Brass, nickel-plated
Order No.	1737950000
Type	ADAP EX 3/4NPT-M32
GTIN (EAN)	4008190958671
Qty.	1 pc(s).

Creation date January 27, 2022 11:58:05 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

ADAP EX 3/4NPT-M32

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 93 g

Temperatures

Operating temperature -40 °C... 100 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Certificate numbers cable gland

Approval conditions	ATEX, IECEX	Certificate no. cable gland (ATEX)	SIRA 10ATEX1225X
Certificate no. cable gland (IECEX)	IECEX SIR 07.0010X	Identification	II 2 GD, Ex d IIC, Ex e II, Ex tD

General information

Cable glands	metric	External thread	3/4" NPT
Internal thread	M 32	Material	Brass, nickel-plated
Note: protection class	Please follow the operating instructions to attain higher IP protection.	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Protection degree	IP54
Protection degree with GWDR	IP54		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [EPLAN, WSCAD](#)
 Catalogues [Catalogues in PDF-format](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1737950000](#)