

KLBU 10-20 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1752701001
Type	KLBU 10-20 CPF
GTIN (EAN)	4032248044436
Qty.	10 pc(s).

KLBUE 10-20 CPF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	39.5 mm	Depth (inches)	1.555 inch
Height	26 mm	Height (inches)	1.024 inch
Width	24 mm	Width (inches)	0.945 inch
Mounting dimension - width	22.5 mm	Net weight	36.048 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	grey
----------	-------	--------	------

System specifications

Version	For a shield connection	Rail	TS 27
---------	-------------------------	------	-------

Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting, Busbar
Type of fixing	when screwed in		

Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	30 mm
-----------------	-------

General

Installation advice	Direct mounting, Busbar	Rail	TS 27
---------------------	-------------------------	------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50		

Approvals

Approvals



ROHS	Conform
------	---------

KLBUE 10-20 CPF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

KLBUE 10-20 CPF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Type	TS 27X12.5M/ST/F.ZN	Version
Order No.	1802690000	Terminal rails, Rail, DIN EN 60715, Steel
GTIN (EAN)	4032248257201	
Qty.	2 m	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1752701001](#)