

**TM 203/20 V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

**General ordering data**

|            |   |
|------------|---|
| Version    | TM, Socket x 6 mm, PVC, Colour: Transparent, Conductor O.D.: 4 - 6 mm |
| Order No.  | <a href="#">1798470000</a>  |
| Type       | TM 203/20 V0  |
| GTIN (EAN) | 4032248243129   |
| Qty.       | 500 pc(s).  |

Creation date January 28, 2022 3:41:44 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## TM 203/20 V0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 6 mm   | Depth (inches)  | 0.236 inch |
| Height     | 20 mm  | Height (inches) | 0.787 inch |
| Width      | 6 mm   | Width (inches)  | 0.236 inch |
| Net weight | 0.35 g |                 |            |

### Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

### General data

|                                   |             |                                   |                           |
|-----------------------------------|-------------|-----------------------------------|---------------------------|
| Colour                            | Transparent | Material                          | PVC                       |
| Operating temperature range       | -40...80 °C | Operating temperature range, max. | 80 °C                     |
| Operating temperature range, min. | -40 °C      | Recommended industries            | Transportation, Machinery |
| Type of printing                  | neutral     | UL 94 flammability rating         | V-0                       |
| Width                             | 6 mm        |                                   |                           |

### Conductor and cable markers

|                               |                     |                                  |                          |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 4 - 6 mm            | Conductor O.D., max.             | 6 mm                     |
| Conductor O.D., min.          | 4 mm                | Conductor cross-section, max.    | 10 mm <sup>2</sup>       |
| Conductor cross-section, min. | 2.5 mm <sup>2</sup> | Cross-section for connected wire | 2.5 - 10 mm <sup>2</sup> |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 |             |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Engineering Data            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>   |
| Product Change Notification | <a href="#">PCN Transparent Sleeves_DE</a><br><a href="#">PCN Transparent Sleeves_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1798470000](#)