

**TM 202/18 V0****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

**General ordering data**

Version	TM, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 2 - 4 mm
Order No.	<a href="#">1798530000</a>
Type	TM 202/18 V0
GTIN (EAN)	4032248243198
Qty.	1,000 pc(s).

Creation date January 28, 2022 3:39:38 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

## TM 202/18 V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	18 mm	Height (inches)	0.709 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	0.455 g		

## Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

## General data

Colour	Transparent	Material	PVC
Operating temperature range	-40...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Recommended industries	Transportation, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Width	5 mm		

## Conductor and cable markers

Conductor O.D.	2 - 4 mm	Conductor O.D., max.	4 mm
Conductor O.D., min.	2 mm	Conductor cross-section, max.	2.5 mm <sup>2</sup>
Conductor cross-section, min.	0.5 mm <sup>2</sup>	Cross-section for connected wire	0.5 - 2.5 mm <sup>2</sup>

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Product Change Notification	<a href="#">PCN Transparent Sleeves_DE</a> <a href="#">PCN Transparent Sleeves_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## TM 202/18 V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	TM-I 18 MC NE WS	Version
Order No.	<a href="#">1718431044</a>	TM-I, Insert markers, 18 x 4 mm, white
GTIN (EAN)	4008190349011	
Qty.	320 pc(s).	
Type	TM-I 18 MC NE RT	Version
Order No.	<a href="#">1718431686</a>	TM-I, Insert markers, 18 x 4 mm, red
GTIN (EAN)	4008190397449	
Qty.	320 pc(s).	
Type	TM-I 18 MC NE GE	Version
Order No.	<a href="#">1718431687</a>	TM-I, Insert markers, 18 x 4 mm, yellow
GTIN (EAN)	4008190349028	
Qty.	320 pc(s).	
Type	TM-I 18 MC NE GN	Version
Order No.	<a href="#">1718431688</a>	TM-I, Insert markers, 18 x 4 mm, green
GTIN (EAN)	4008190398699	
Qty.	320 pc(s).	
Type	TM-I 18 MC NE BL	Version
Order No.	<a href="#">1718431693</a>	TM-I, Insert markers, 18 x 4 mm, blue
GTIN (EAN)	4008190397432	
Qty.	320 pc(s).	

## TM 202/18 V0

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	TM-I 12/18 MC NE GE	Version
Order No.	<a href="#">1409630000</a>	TM-I, Insert markers, 30 x 4 mm, yellow
GTIN (EAN)	4050118210835	
Qty.	240 pc(s).	
Type	TM-I 12/18 MC NE RT	Version
Order No.	<a href="#">1421170000</a>	TM-I, Insert markers, 30 x 4 mm, red
GTIN (EAN)	4050118224931	
Qty.	240 pc(s).	
Type	TM-I 12/18 MC NE GN	Version
Order No.	<a href="#">1421150000</a>	TM-I, Insert markers, 30 x 4 mm, green
GTIN (EAN)	4050118224870	
Qty.	240 pc(s).	
Type	TM-I 12/18 MC NE BL	Version
Order No.	<a href="#">1421160000</a>	TM-I, Insert markers, 30 x 4 mm, blue
GTIN (EAN)	4050118225006	
Qty.	240 pc(s).	
Type	TM-I 12/18 MC NE WS	Version
Order No.	<a href="#">1323730000</a>	TM-I, Insert markers, 30 x 4 mm, white
GTIN (EAN)	4050118126785	
Qty.	240 pc(s).	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1798530000](#)